ENPULSION

MICRO R³

FEEP | FIELD EMISSION

as of Mai 202

Building on the heritage of the ENPULSION NANO, ENPULSION has developed a scaled version of the technology to target *small and medium size spacecrafts*. The **ENPULSION MICRO R³** is engineered in a modular approach, with units clustering easily together to form building blocks that can be arranged for various mission profiles. *The first model was successfully operated in space in Q1/2021*.





MATURE TECHNOLOGY

The ENPULSION MICRO R³ is a scaled technology of the ENPULSION NANO with a developmental history of over 15 years. During this time, there have been hundreds of emitters tested with an ongoing lifetime test that has surpassed 30 000 hours of firing. This endurance test continues without degradations.



MODULAR PACKAGE WITH HIGH TOTAL IMPULSE

One module and its tank only take up a volume of 1.6 L and can provide more than 50 000 Ns at 4 000 s lsp. The module is simply bolted to the outside of the spacecraft and can be used as a standalone unit or easily be clustered for higher thrust applications.



DYNAMIC PRECISE THRUST CONTROL

Thrust can be controlled through the electrode voltage, which provides excellent controllability, down to a precision of 50 μ N with low thrust noise.



DEBRIS SAFETY

Even during active operation, no part of the thruster is pressurized, and no chemical energy is stored. This means that in case of a collision or impact, there will not be an explosive reaction which could harm the spacecraft and create debris.



CONTROLLABLE SPECIFIC IMPULSE UP TO 4500 S

With its efficient ionization process the ENPULSION MICRO R³ can deliver higher specific impulse than any other ion propulsion system currently on the market. The thruster is capable of a range of Isp from 1000 s to 4500 s.



HERITAGE ELECTRONICS

The Power Processing Unit is based on the heritage electronics used in the ENPULSION NANO, leveraging exhaustive on-orbit and testing heritage, as well as introducing component lot control and heritage in EEE part selection. The PPU can be either stacked or integrated separately from the thruster.



SAFE AND INERT SYSTEM COMPLIANT DURING LAUNCH

The FEEP technology contains no moving parts and uses non-toxic indium as propellant. There are neither liquids or reactive propellants nor pressurized vessels. Stored as a solid and filled at our factory it requires no special handling, integration, or launch procedures.



4 Emitters, reservoir for 1.3 kg of indium in a 14 x 12 x 10 cm envelope.

Each emitter is identical to the one used in the ongoing lifetime test (>30 000 h).



MICRO R³


PROPERTIES AND PERFORMANCE





Separate integration of thruster head and PPU

The ENPULSION MICRO R³ can be integrated in a stacked configuration, with the PPU situated directly underneath the thruster head, with same footprint. Alternatively, the PPU box can be integrated separately from the thruster head.



DYNAMIC THRUST RANGE:1	300 μN-1 mN
NOMINAL THRUST:	1 mN
SPECIFIC IMPULSE:	1500-4500 s
PROPELLANT MASS:	1.3 kg
TOTAL IMPULSE:2	UP TO 50kNs
POWER AT NOMINAL THRUST:	105 W
MASS (DRY/WET):	2.6 kg (DRY) INCL. PPU
	3.9 kg (WET) INCL. PPU
TOTAL SYSTEM POWER:	30-120 W
HOT STANDBY POWER:3	10 – 15 W
OUTSIDE DIMENSIONS:	
THRUSTER HEAD PPU BOX	140 × 120 × 98.6 mm 140 × 120 × 34.0 mm

Since the founding of the company in 2016 we have delivered to customers *hundreds of thrusters, more than* 100 of which are currently in space. We have, therefore, developed an empirical understanding of the intrinsic variation of the performance and parameters of emitters in these thrusters in their production process and in their application in different types of missions. This enables us, starting from January 1st, 2022, to offer you our new **Emitter Selection Service** which allows you to select between *three distinct types of crown emitters*:

- \triangleright Alpha (α) emitters provide the best balance between price, performance, and guaranteed delivery times. This is the perfect solution for commercial constellation applications.
- \triangleright BETA (β) emitters are the best solution whenever cost optimization is the most important driver.
- SAMMA (γ) emitters are hand-picked for their guaranteed peak performance and especially appropriate for your missions in deep space, exploration, and others where emitter output needs to be taken to extremes.

¹ The ENPULSION MICRO R³ can be operated at a wide range of thrust and specific impulse, depending on the power level available. The operational envelope is based on total system power including typical heater and neutralizers consumption. Performances shown above correspond to maximum thrust to power curves for different grades of emitters.

² Strongly depends on emitter option. See performance map for selection options.

³ Depends on accommodation and resulting thermal environment.